TITANTAG™ Nail^{1/2}

Frequency	UHF
Protocol	ISO18000-6-C EPC C1G2
Region	EU
Dimensions (mm)	W13 H7 T2.1
Silicon chip	Alien Higgs3
Memory (bits)	TOTAL 800
	EPC up to 480
	User up to 512
Metal friendly	Both on/off metal
Reads up to meters	0.2 (On metal)
	0.2 (Off metal)
Operating temperature	-45<>85°C
Storage temperature	-45<>150°C
IP class	IP68
Year of release	2016
Product code	130721G


Nail Alien Higgs3 15*10*2.1 0.2 0.3 Inch TN Alien Higgs3 26*10*2.1 0.7 0.5 Inch Alien Higgs3 26*10*3.1 1.0 0.6 Inch SQ Alien Higgs3 26*26*3.1 1.5 1.0 Inch SQ HT Alien Higgs3 36*26*2.5 2.5 n/a Tray NM Impinj Monza4 35*15*3.1 n/a 1.0 Smallest Alien Higgs3 39*10*3.1 2.5 0.5 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*3.1 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*44*1.4 n/a 3.5 Spiral Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 60*6*3.1 2.0 0.5 General TN Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 92*16*3.1 3.5 1.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic Alien Higgs3 92*16*5.2 3.5 n/a Basic Alien Higgs3 92*16*5.2 3.5 n/a Basic Alien Higgs3 95*25*3.1 4.0 6.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a		Silicon chips	W*H*T	Read (up to meters)	
Nail Alien Higgs3 15*10*2.1 0.2 0.3 Inch TN Alien Higgs3 26*10*2.1 0.7 0.5 Inch Alien Higgs3 26*10*3.1 1.0 0.6 Inch SQ Alien Higgs3 26*26*3.1 1.5 1.0 Inch SQ HT Alien Higgs3 26*26*2.5 2.5 n/a Tray NM Impinj Monza4 35*15*3.1 n/a 1.0 Smallest Alien Higgs3 39*10*3.1 2.5 1.0 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 75*16*2.1 2.5 2.0 General TN <td></td> <td>Silicon emps</td> <td>(mm)</td> <td>On metal</td> <td>Off metal</td>		Silicon emps	(mm)	On metal	Off metal
Inch TN Alien Higgs3 26*10*2.1 0.7 0.5 Inch Alien Higgs3 26*10*3.1 1.0 0.6 Inch SQ Alien Higgs3 26*26*3.1 1.5 1.0 Inch SQ HT Alien Higgs3 26*26*2.5 2.5 n/a Tray NM Impinj Monza4 35*15*3.1 n/a 1.0 Smallest Alien Higgs3 39*10*3.1 2.5 1.0 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic Alien Higgs3 92*16*5.2 3.5 n/a Basic Alien Higgs3 94*11*1.4 n/a 5.0 Basic Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener MAG Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*3.1 5.0 n/a					
Inch Alien Higgs3 26*10*3.1 1.0 0.6 Inch SQ Alien Higgs3 26*26*3.1 1.5 1.0 Inch SQ HT Alien Higgs3 26*26*2.5 2.5 n/a Tray NM Impinj Monza4 35*15*3.1 n/a 1.0 Smallest Alien Higgs3 39*10*3.1 2.5 1.0 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*41*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 60*6*3.1 2.0 0.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 92*16*3.1 3.5 1.0 Basic Alien Higgs3 92*16*3.1 3.5 5.0 Basic Alien Higgs3 95*25*3.1 4.0 6.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0	Nail	Alien Higgs3	15*10*2.1	0.2	0.3
Inch SQ Alien Higgs3 26*26*3.1 1.5 1.0 Inch SQ HT Alien Higgs3 26*26*2.5 2.5 n/a Tray NM Impinj Monza4 35*15*3.1 n/a 1.0 Smallest Alien Higgs3 39*10*3.1 2.5 1.0 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic Alien Higgs3 92*16*3.1 3.5 5.0 Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 139*6*4.0 6.0 5.0 Fastener MAG Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Inch TN	Alien Higgs3	26*10*2.1	0.7	0.5
Inch SQ HT Alien Higgs3 26*26*2.5 2.5 n/a Tray NM Impinj Monza4 35*15*3.1 n/a 1.0 Smallest Alien Higgs3 39*10*3.1 2.5 1.0 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 75*16*2.1 2.5 2.0 General TN Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 92*16*5.2 3.5 n/a Secu	Inch	Alien Higgs3	26*10*3.1	1.0	0.6
Tray NM Impinj Monza4 35*15*3.1 n/a 1.0 Smallest Alien Higgs3 39*10*3.1 2.5 1.0 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 94*11*1.4 n/a 5.0 Secure	Inch SQ	Alien Higgs3	26*26*3.1	1.5	1.0
Smallest Alien Higgs3 39*10*3.1 2.5 1.0 Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*3.1 3.5 1.0 Basic L Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 95*25*3.1 4.0 6.0 Secure<	Inch SQ HT	Alien Higgs3	26*26*2.5	2.5	n/a
Smallest AC Alien Higgs3 39*10*3.1 2.5 0.5 Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*3.1 3.5 1.0 Basic L Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 139*6*4.0 6.0 5.0 Fasten	Tray NM	Impinj Monza4	35*15*3.1	n/a	1.0
Smallest MAG Alien Higgs3 39*10*4.8 1.5 n/a Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 94*11*1.4 n/a 5.0 Pallet Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener Alien Higgs3 148*18*7.1 5.0 n/a	Smallest	Alien Higgs3	39*10*3.1	2.5	1.0
Tray E Alien Higgs3 40*13*4.1 3.0 2.0 Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 92*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*5.2 3.5 n/a Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 94*11*1.4 n/a 5.0 Pallet Alien Higgs3 95*25*3.1 4.0 6.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 139*6*4.0 6.0 5.0 Fastener	Smallest AC	Alien Higgs3	39*10*3.1	2.5	0.5
Smallest NM Alien Higgs3 45*10*3.1 n/a 3.5 Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Hlggs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 92*16*5.2 3.5 n/a Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Smallest MAG	Alien Higgs3	39*10*4.8	1.5	n/a
Spiral Alien Higgs3 45*44*1.4 n/a 1.0 Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 92*16*5.2 3.5 n/a Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Tray E	Alien Higgs3	40*13*4.1	3.0	2.0
Strip Alien Higgs3 60*6*3.1 2.0 0.5 Laundry Alien Higgs3 68*9*0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 92*16*5.2 3.5 n/a Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Smallest NM	Alien Higgs3	45*10*3.1	n/a	3.5
Laundry Alien Higgs3 68*9 *0.4 n/a 2.5 General TN Alien Higgs3 75*16*2.1 2.5 2.0 General Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 92*16*5.2 3.5 n/a Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Spiral	Alien Higgs3	45*44*1.4	n/a	1.0
General TN Alien Higgs3 75*16*2.1 2.5 2.0 General Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 92*16*5.2 3.5 n/a Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Strip	Alien HIggs3	60*6*3.1	2.0	0.5
General Alien Higgs3 75*16*3.1 3.5 2.0 General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 110*20*3.1 6.5 3.0 Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Laundry	Alien Higgs3	68*9 *0.4	n/a	2.5
General AC Alien Higgs3 75*16*3.1 3.5 2.0 Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 110*20*3.1 6.5 3.0 Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	General TN	Alien Higgs3	75*16*2.1	2.5	2.0
Basic Alien Higgs3 92*16*3.1 3.5 1.0 Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 110*20*3.1 6.5 3.0 Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	General	Alien Higgs3	75*16*3.1	3.5	2.0
Basic MAG Alien Higgs3 92*16*5.2 3.5 n/a Basic L Alien Higgs3 110*20*3.1 6.5 3.0 Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	General AC	Alien Higgs3	75*16*3.1	3.5	2.0
Basic L Alien Higgs3 110*20*3.1 6.5 3.0 Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Basic	Alien Higgs3	92*16*3.1	3.5	1.0
Pallet Alien Higgs3 94*11*1.4 n/a 5.0 Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Basic MAG	Alien Higgs3	92*16*5.2	3.5	n/a
Secure Alien Higgs3 95*25*3.1 4.0 6.0 Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Basic L	Alien Higgs3	110*20*3.1	6.5	3.0
Secure HT Alien Higgs3 95*25*2.5 5.0 n/a Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Pallet	Alien Higgs3	94*11*1.4	n/a	5.0
Blade Alien Higgs3 139*6*4.0 6.0 5.0 Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Secure	Alien Higgs3	95*25*3.1	4.0	6.0
Fastener Alien Higgs3 148*18*3.1 6.0 8.0 Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Secure HT	Alien Higgs3	95*25*2.5	5.0	n/a
Fastener MAG Alien Higgs3 148*18*7.1 5.0 n/a	Blade	Alien Higgs3	139*6*4.0	6.0	5.0
•	Fastener	Alien Higgs3	148*18*3.1	6.0	8.0
	Fastener MAG	Alien Higgs3	148*18*7.1	5.0	n/a
Fastener TK Alien Higgs3 148*18*4.1 12.0 11.0	Fastener TK	Alien Higgs3	148*18*4.1	12.0	11.0
4KB5M Fujitsu 803A 163*30*4.1 2.5 2.0	4KB5M	Fujitsu 803A	163*30*4.1	2.5	2.0



[1] Nail^{1/2} Feature



[2] Nail^{1/2} Dimensions (mm)



[3] Key materials and processes

Silicon chip Alien Higgs3

- Read sensitivity of -20dBm Best performing among UHF Gen 2 RFID chips
- Total 800bits memory EPC 96bits (extensible to 480bits), User 512bits, TID 64 bits, Access& Kill password each 32bits and Lock password 64bits
- Most widely adopted chip for metal mounting UHF RFID tags
- RFcamp has adopted Alien Higgs3 since year of 2008.

www.alientechnology.com/wp-content/uploads/ALC-360%20Higgs3%202014-12-21.pdf

Antenna PCB FR4, Copper etched, Gold plated

- FR4 (Fire retardant 4, composed of woven fiberglass cloth with an epoxy resin binder) Most stable and widely applied antenna materials in recent 30 years worldwide, with highest durability and consistent electrical property
- Copper etched antenna has much higher accuracy with lower tolerance than aluminum etched antenna and conductive ink printed antenna, which makes tag performance more consistent with lower read range variance.
- Gold is plated on chip bonded area of copper etched antenna, in order to enhance chip adhesion on antenna as well as electrical interconnection with antenna.

Packaging Double layer PCBs, laminated under high temperature and pressure

- Tag antenna has convoluted structure of two or three layers with copper ground plane, so tag is composed of double layer PCBs, tightly combined and laminated under high pressure and temperature of 200 $^{\circ}$ C for >2 hours.
- Many tag makers copy TITANTAG™ in appearance, but they can not copy tags' durability and read consistency.
- Surface of PCBs is coated with TOYO (black) PSR, best of kind which can protect it against electrical stress and water ingression.

Chip bonding Wire bonded, aluminum or gold

- Unlike other tag makers using flip chip bonding or chip soldering, RFcamp has adopted wire bonding technology since year of 2004.
- Wire bonding, though most complicated and expensive chip bonding method, is most stable in electrical interconnection and most durable in mechanical and temperature stresses. It, with highest precision, is also best fit for working on complicated antenna patterns of double layer PCBs.



[4] Nail^{1/2} Durability

• Temperature stress

Test methods	Descriptions	Pass/Fail
150℃, 6hrs	Stored in convection oven at 150C, 6hrs	Pass
-45<>85 ℃, 50 cycles	Stored in temperature shock chamber for 50 cycles One cycle includes 30 min. at-45C, 30 min, transition, 30min. at 85C and 30min. transition.	Pass
85 ℃/85%, 24hrs	Stored in humidity chamber at 85C/85%RH for 24 hours	Pass
Boling water, 6 hrs	Immersed in boiling water for 6 hours	Pass

• Ingression www.dsmt.com/resources/ip-rating-chart

IP Class IP68 1.5

Mechanical stress

Test methods	Descriptions	Pass/Fail
Iron ball fall test	Free fall of 1kg iron ball from 1.5meters height on any side of tag - 10 times	Pass
Vibration	IEC60068-2-6/64	Pass
Drop& topple	IEC60068-2-31	Pass
Shock (acceleration)	IEC60068-2-22	Pass
Pressure	50 Bar on any side of tag, 10 times	Pass

• Chemical stress

Chemicals	Descriptions	Pass/Fail
Alkali	NaOH (10%, pH13) Immersed 24 hrs.	Pass
Acid	Sulfuric acid (10%, pH2) Immersed 24 hrs.	Pass
Petroleum	Gasoline, Diesel, Kerosene, lubricating oil Immersed 24 hrs.	Pass
Alcohol	Methanol, Ethanol Immersed 24 hrs.	Pass
Surfactant	Solvent for metal tool oils Immersed 24 hrs.	Pass
Salt water	IEC60068-2-11	Pass

Electrical stress

• Radiation stress (N/A)

Gamma ray	kGy	
-----------	-----	--

Autoclave stress (N/A)

Autoclave conditio	Sterilization processes
Autociave conditio	Sterilization processes



[5] Nail^{1/2} Options

Chip encoding service

- •Encodes EPC memory sector only*.
- •Encodes tags with 4 multiple digits from 16 bits (4 digits decimal or hex or ASCII) up to 480 bits (120 digits decimal or hex or ASCII) upon customers' request.
- •Unless requested by customer, all tags are encoded with 24 digits decimal (Date 8 digits + Serial 16 digits), before shipped to customers. For example, code 201508140000000000001278 tells that tag was 1278th encoded on August 14, 2015.
- •Tag code can be permanently locked with password of 8 digits decimal or hex, upon customer's request.
- * For special encoding service (e.g. TID to EPC or user memory encoding), please ask RFcamp.

• Label& printing service (Not applicable to this product)

 Provides fast and reasonably priced custom label service with printing variable data, barcode and logo.
 Label material is water proof and "hard to tear off" polysynthetic.





Laser engraving& direct printing service

- •With CO2 laser, tag surface is precisely and permanently etched into variable data, barcode and logo with black and yellow contrast.
- With silk screen printing or pad printing method, tag surface is permanently printed with various colored logo or text.







Backing adhesive

- •Unless requested otherwise, RFcamp recommends and applies 3M468MP or 3M9472LE (Aka. 3M300LSE) double sided adhesive tapes for general applications. For harsh environments, RFcamp recommends 3M VHB tapes.
- For stronger adhesion, RFcamp suggests glue solutions such as Cemedine's Super X or Loctite's double compound epoxies.
- For special solution, please ask RFcamp.

Fasteners& brackets (Not applicable to this product)

- •For some small TITANTAGs, metal fastener may adversely affect tag read performance, so please ask RFcamp for suitable solution.
- Upon customer's request,
 RFcamp develops metal based brackets for special applications, with optimal tag performance.







Encapsulations

•For special environment requiring enhanced chemical durability, RFcamp applies special coating materials over tag.
•Upon customer's request, RFcamp develops injection molded ruggedized case or rubber (polyurethane or silicone) based encapsulation.





